



\* Representative image

## T181061

by Acme Electric  
Catalog ID: T181061

Prop65\_Cancer&Reproductive

Buck-Boost Transformer - Single Phase, 240 X 480 - 24/48V, 50VA

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in kVA

## Product Details

### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Buck-Boost Transformer
Secondary Voltage	24/48 V
UL Insulation Class	180°C
UPC	047503087503
Winding Material	CU
kVA	0.05

### Dimensions

Height	9.68 in
Length	4.51 in
Weight	4 lb
Width	4.75 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	240 X 480 V

### Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 506