



* Representative image

T2527071

by Acme Electric
Catalog ID: T2527071

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 600/480 - 480/380V, 45/36kVA, Autotransformer

- Quiet operation with sound levels below NEMA standards

Product Details

General

BNFC Taps	2
Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480/380 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	004750342007
Winding Material	AL
kVA	45/36

Dimensions

Height	15.21 in
Length	7.37 in
Weight	156 lb
Width	19.25 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600/480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506