



\* Representative image

## T253008SS

by Acme Electric  
Catalog ID: T253008SS

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 0.5kVA, 316 Stainless Steel

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	155°C
UPC	047503130513
Winding Material	CU
kVA	0.5

### Dimensions

Height	9.06 in
Length	4.2 in
Weight	15 lb
Width	4.37 in

### Electrical Ratings

Frequency Rating	50/60 Hz
------------------	----------

Primary Voltage	240 X 480 V
-----------------	-------------

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506