



* Representative image

T253012SS

by Acme Electric

Catalog ID: T253012SS

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 2kVA, 316 Stainless Steel

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503085783
Winding Material	CU
kVA	2

Dimensions

Height	13 in
Length	5.13 in
Weight	38 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Primary Voltage	240 X 480 V
-----------------	-------------

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506