



\* Representative image

## T253013SS

by Acme Electric

Catalog ID: T253013SS

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 3kVA, 316 Stainless Steel

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

|                      |                                   |
|----------------------|-----------------------------------|
| ANFC Taps            | 2                                 |
| BNFC Taps            | 2                                 |
| Construction         | Encapsulated                      |
| Electrostatic Shield | Shielded                          |
| Max Temperature Rise | 115 Degrees Celsius               |
| Mounting Type        | Wall                              |
| Primary Voltage      | 240 X 480                         |
| Product Category     | Dry Type Distribution Transformer |
| Secondary Voltage    | 120/240 V                         |
| Taps % Steps         | 2.5%                              |
| UL Insulation Class  | 180°C                             |
| UPC                  | 047503084342                      |
| Winding Material     | CU                                |
| kVA                  | 3                                 |

### Dimensions

|        |          |
|--------|----------|
| Height | 11.5 in  |
| Length | 7.13 in  |
| Weight | 55 lb    |
| Width  | 10.31 in |

## Electrical Ratings

|                  |             |
|------------------|-------------|
| Frequency Rating | 60 Hz       |
| Primary Voltage  | 240 X 480 V |

## Certifications and Compliance

|              |              |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating  | NEMA 3R      |
| UL Standard  | UL 506       |