



\* Representative image

## T253061

by Acme Electric  
Catalog ID: T253061

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240 - 120/240V,  
1.5kVA, Autotransformer

- Quiet operation with sound levels below NEMA standards

## Product Details

### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503087763
Winding Material	CU
kVA	1.5

### Dimensions

Height	9.68 in
Length	4.51 in
Weight	19 lb
Width	4.5 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506