



* Representative image

T253062

by Acme Electric

Catalog ID: T253062

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240 - 120/240V, 2kVA, Autotransformer

- Quiet operation with sound levels below NEMA standards

Product Details

General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503086032
Winding Material	CU
kVA	2

Dimensions

Height	10.5 in
Length	5.13 in
Weight	24 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506