



\* Representative image

## T253067

by Acme Electric  
Catalog ID: T253067

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240 - 120/240V,  
15kVA, Autotransformer

- Quiet operation with sound levels below NEMA standards

## Product Details

### General

Construction	Encapsulated
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503735329
Winding Material	CU
kVA	15

### Dimensions

Height	15.19 in
Length	10.84 in
Weight	115 lb
Width	13.5 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506