



* Representative image

T253108S

by Acme Electric
Catalog ID: T253108S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V,
0.5kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	155°C
UPC	047503732601
Winding Material	CU
kVA	0.5

Dimensions

Height	9.06 in
Length	4.2 in
Weight	15 lb
Width	4.37 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506