



\* Representative image

## T253109S

by Acme Electric  
Catalog ID: T253109S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V,  
0.75kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	155°C
UPC	047503732656
Winding Material	CU
kVA	0.75

### Dimensions

Height	9.68 in
Length	4.5 in
Weight	19 lb
Width	4.75 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506