



* Representative image

T253112S

by Acme Electric
Catalog ID: T253112S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 2kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503732809
Winding Material	CU
kVA	2

Dimensions

Height	13 in
Length	5.13 in
Weight	38 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506