



* Representative image

T253517SS

by Acme Electric

Catalog ID: T253517SS

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 240X480 - 120/240V, 15kVA, 316 Stainless Steel

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240 X 480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503130605
Winding Material	CU
kVA	15

Dimensions

Height	16.94 in
Length	11.59 in
Weight	170 lb
Width	14.12 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240 X 480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506