



* Representative image

T2536161S

by Acme Electric
Catalog ID: T2536161S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 10kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

| | |
|----------------------|-----------------------------------|
| BNFC Taps | 2 |
| Construction | Encapsulated |
| Electrostatic Shield | Shielded |
| Max Temperature Rise | 115 Degrees Celsius |
| Mounting Type | Wall |
| Primary Voltage | 600 |
| Product Category | Dry Type Distribution Transformer |
| Secondary Voltage | 120/240 V |
| Taps % Steps | 5% |
| UL Insulation Class | 180°C |
| UPC | 047503734506 |
| Winding Material | CU |
| kVA | 10 |

Dimensions

| | |
|--------|----------|
| Height | 15.19 in |
| Length | 10.84 in |
| Weight | 125 lb |
| Width | 13.5 in |

Electrical Ratings

| | |
|------------------|-------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 600 V |

Certifications and Compliance

| | |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating | NEMA 3R |

| | |
|-------------|--------|
| UL Standard | UL 506 |
|-------------|--------|