



* Representative image

T2536181S

by Acme Electric
Catalog ID: T2536181S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Single Phase, 600 - 120V/240V, 25kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503734605
Winding Material	CU
kVA	25

Dimensions

Height	18.44 in
Length	13.34 in
Weight	250 lb
Width	16.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R

UL Standard	UL 506
-------------	--------