



* Representative image

T279740S

by Acme Electric
Catalog ID: T279740S

Prop65_Cancer&Reproductive

120/208/240/277 Primary Volts - 120/240 Secondary Volts - 1Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 / 208 / 240 / 277 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503102008
Winding Material	CU
kVA	1

Dimensions

Height	10.5 in
Length	5.13 in
Weight	23 lb
Width	5.5 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506