



* Representative image

T279743S

by Acme Electric
Catalog ID: T279743S

Prop65_Cancer&Reproductive

120/208/240/277 Primary Volts - 120/240 Secondary Volts - 1Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 / 208 / 240 / 277 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503102060
Winding Material	CU
kVA	3

Dimensions

Height	11.5 in
Length	7.13 in
Weight	55 lb
Width	10.31 in

Electrical Ratings

Frequency Rating	60 Hz
------------------	-------

Primary Voltage	120/208/240/277 V
-----------------	-------------------

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506