



\* Representative image

## T279748S

by Acme Electric  
Catalog ID: T279748S

Prop65\_Cancer&Reproductive

120/208/240/277 Primary Volts - 120/240 Secondary Volts - 1Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	120 / 208 / 240 / 277 V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	120/240 V
UL Insulation Class	180°C
UPC	047503102169
Winding Material	CU
kVA	25

### Dimensions

Height	18.44 in
Length	13.34 in
Weight	261 lb
Width	16.13 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	120/208/240/277 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506