



* Representative image

T2A527131

by Acme Electric
Catalog ID: T2A527131

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 600/480 - 480/380V, 150/120kVA, Autotransformer

- Quiet operation with sound levels below NEMA standards
- Optional weather shield - WSA1

Product Details

General

BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480/380 V
Taps % Steps	5.0%
UL Insulation Class	220°C
UPC	047503420133
Winding Material	AL
kVA	150/120

Dimensions

Height	25.5 in
Length	19.4 in
Weight	350 lb
Width	24.4 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600/480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561