



* Representative image

T2A527151

by Acme Electric
Catalog ID: T2A527151

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 600/480 - 480/380V, 225/180kVA, Autotransformer

- Quiet operation with sound levels below NEMA standards
- Optional weather shield - WSA2

Product Details

General

BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480/380 V
Taps % Steps	5.0%
UL Insulation Class	220°C
UPC	047503420157
Winding Material	AL
kVA	225/180

Dimensions

Height	29.41 in
Length	22.37 in
Weight	600 lb
Width	28.15 in

Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600/480 V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561