



\* Representative image

## T2A527181

by Acme Electric  
Catalog ID: T2A527181

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 600/480 -  
480/380V, 450/360kVA, Autotransformer

- Quiet operation with sound levels below NEMA standards
- Optional weather shield - WSA3

## Product Details

### General

BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600/480
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480/380 V
Taps % Steps	5.0%
UL Insulation Class	220°C
UPC	047503420010
Winding Material	AL
kVA	450/360

### Dimensions

Height	35.47 in
Length	26.88 in
Weight	750 lb
Width	31.9 in

### Electrical Ratings

Frequency Rating	50/60 Hz
Primary Voltage	600/480 V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 2
UL Standard	UL 1561