



\* Representative image

## T2A533291S

by Acme Electric  
Catalog ID: T2A533291S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 480Δ - 240Δ/120V, 6kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	240D 120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503733752
Winding Material	AL
kVA	6

### Dimensions

Height	11.83 in
Length	8.82 in
Weight	140 lb
Width	14.17 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506