



\* Representative image

## T2A533601S

by Acme Electric

Catalog ID: T2A533601S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 240Δ - 208Y/120V, 9kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	240Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503733905
Winding Material	AL
kVA	9

### Dimensions

Height	14.03 in
Length	11.52 in
Weight	180 lb
Width	17.77 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506