



\* Representative image

## T2A792681S

by Acme Electric  
Catalog ID: T2A792681S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 208Δ - 208Y/120V, 3kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	208Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503089217
Winding Material	CU
kVA	3

### Dimensions

Height	10.38 in
Length	7.47 in
Weight	75 lb
Width	12.37 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	208D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506