



* Representative image

T2A792701S

by Acme Electric
Catalog ID: T2A792701S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 208Δ - 208Y/120V, 9kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

| | |
|----------------------|-----------------------------------|
| BNFC Taps | 2 |
| Construction | Encapsulated |
| Electrostatic Shield | Shielded |
| Max Temperature Rise | 115 Degrees Celsius |
| Mounting Type | Wall |
| Primary Voltage | 208Δ |
| Product Category | Dry Type Distribution Transformer |
| Secondary Voltage | 208Y/120 V |
| Taps % Steps | 5.0% |
| UL Insulation Class | 180°C |
| UPC | 004750379270 |
| Winding Material | AL |
| kVA | 9 |

Dimensions

| | |
|--------|----------|
| Height | 14.03 in |
| Length | 11.52 in |
| Weight | 180 lb |
| Width | 17.77 in |

Electrical Ratings

| | |
|------------------|--------|
| Frequency Rating | 60 Hz |
| Primary Voltage | 208D V |

Certifications and Compliance

| | |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
| Nema Rating | NEMA 3R |
| UL Standard | UL 506 |