



* Representative image

T2A793321S

by Acme Electric

Catalog ID: T2A793321S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 600Δ - 208Y/120V, 9kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503722329
Winding Material	AL
kVA	9

Dimensions

Height	14.03 in
Length	11.52 in
Weight	180 lb
Width	17.77 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506