



\* Representative image

## T2A795161S

by Acme Electric  
Catalog ID: T2A795161S

Prop65\_Cancer&Reproductive

600Δ Primary Volts - 480Y/277 Secondary Volts - 3Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503420508
Winding Material	CU
kVA	3

### Dimensions

Height	10.38 in
Length	7.47 in
Weight	75 lb
Width	12.37 in

## Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	600D V

## Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506