



* Representative image

T2A795533S

by Acme Electric
Catalog ID: T2A795533S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 380Δ - 220Y/127V, 45kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA2

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	380Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	220Y/127 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503795538
Winding Material	AL
kVA	45

Dimensions

Height	29.41 in
Length	22.37 in
Weight	468 lb
Width	28.15 in

Electrical Ratings

Frequency Rating	50 Hz
Primary Voltage	380D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 2
UL Standard	UL 1561