



* Representative image

T2A795543S

by Acme Electric
Catalog ID: T2A795543S

Prop65_Cancer&Reproductive

380Δ Primary Volts - 220Y/127 Secondary Volts - 3Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection
- Optional weather shield - WSA3

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	380Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	220Y/127 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503795545
Winding Material	AL
kVA	75

Dimensions

Height	35.47 in
Length	26.88 in
Weight	693 lb
Width	31.9 in

Electrical Ratings

Frequency Rating	50 Hz
Primary Voltage	380D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 2
UL Standard	UL 1561