



* Representative image

T3001M0012B

by Acme Electric
Catalog ID: T3001M0012B

Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 1000kVA

- Quiet operation with sound levels below NEMA standards

Product Details

General

ANFC Taps	1
BNFC Taps	1
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	220°C
Winding Material	AL
kVA	1000

Dimensions

Height	62.8 in
Length	41.5 in
Weight	5375 lb
Width	54 in

Electrical Ratings

Efficiency	99.28%
Frequency Rating	60 Hz
Primary Voltage	480D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431

Nema Rating	NEMA 3R
UL Standard	UL 1561