



## T3015K0013BC

by Acme Electric  
Catalog ID: T3015K0013BC

Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V,  
15kVA, Copper Windings

- Quiet operation with sound levels below NEMA standards

### Product Details

#### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
Winding Material	CU
kVA	15

#### Dimensions

Height	25.5 in
Length	19.37 in
Weight	290 lb
Width	24.39 in

#### Electrical Ratings

Efficiency	97.89%
Frequency Rating	60 Hz
Primary Voltage	480D V

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R

UL Standard	UL 1561
-------------	---------