



T3015K0064BS

by Acme Electric
Catalog ID: T3015K0064BS

208Δ Primary Volts - 208Y/120 Secondary Volts - 3Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
Winding Material	AL
kVA	15

Dimensions

Height	25.5 in
Length	19.37 in
Weight	290 lb
Width	24.39 in

Electrical Ratings

Efficiency	97.89%
Frequency Rating	60 Hz
Primary Voltage	208D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431

Nema Rating	NEMA 3R
UL Standard	UL 1561