



\* Representative image

## T3030K0034B

by Acme Electric

Catalog ID: T3030K0034B

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 208Δ - 480Y/277V  
30kVA

- Quiet operation with sound levels below NEMA standards

## Product Details

### General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503092903
Winding Material	AL
kVA	30

### Dimensions

Height	25.5 in
Length	19.37 in
Weight	330 lb
Width	24.39 in

### Electrical Ratings

Efficiency	98.23%
Frequency Rating	60 Hz
Primary Voltage	208D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561