



* Representative image

T3030K0093BS

by Acme Electric
Catalog ID: T3030K0093BS

Prop65_Cancer

Low Voltage Distribution Transformer - Three Phase, 600Δ - 480Y/277V, 30kVA, Shielded

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503092965
Winding Material	AL
kVA	30

Dimensions

Height	25.5 in
Length	19.37 in
Weight	400 lb
Width	24.39 in

Electrical Ratings

Efficiency	98.23%
Frequency Rating	60 Hz
Primary Voltage	600D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561