



\* Representative image

## T3030K0170BS

by Acme Electric  
Catalog ID: T3030K0170BS

Prop65\_Cancer

Low Voltage Distribution Transformer - Three Phase,  
190/200/208/220/240Δ - 400Y/231V, 30kVA, Shielded

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

### Product Details

#### General

Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	190 / 200 / 208 / 220 / 240Δ V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	400Y/231 V
UL Insulation Class	220°C
UPC	047503092972
Winding Material	AL/CU
kVA	30

#### Dimensions

Height	25.5 in
Length	19.37 in
Weight	511 lb
Width	24.39 in

#### Electrical Ratings

Efficiency	98.23%
Frequency Rating	60 Hz
Primary Voltage	190/200/208/220/240D V

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R

UL Standard	UL 1561
-------------	---------