



* Representative image

T3045K0013BC

by Acme Electric

Catalog ID: T3045K0013BC

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 45kVA, Copper Windings

- Quiet operation with sound levels below NEMA standards

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503092996
Winding Material	CU
kVA	45

Dimensions

Height	25.5 in
Length	19.37 in
Weight	397 lb
Width	24.39 in

Electrical Ratings

Efficiency	98.40%
Frequency Rating	60 Hz
Primary Voltage	480D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561