



\* Representative image

## T3045K0013BSB

by Acme Electric  
Catalog ID: T3045K0013BSB

Prop65\_Cancer

Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V,  
45kVA, 80°C, Shielded

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

### Product Details

#### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	80 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503093009
Winding Material	AL
kVA	45

#### Dimensions

Height	29.41 in
Length	22.37 in
Weight	500 lb
Width	28.15 in

#### Electrical Ratings

Efficiency	98.40%
Frequency Rating	60 Hz
Primary Voltage	480D V

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561