



* Representative image

T3045K0053B

by Acme Electric

Catalog ID: T3045K0053B

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 480Δ - 480Y/277V, 45kVA

- Quiet operation with sound levels below NEMA standards

Product Details

General

| | |
|----------------------|-----------------------------------|
| ANFC Taps | 2 |
| BNFC Taps | 4 |
| Construction | Ventilated |
| Max Temperature Rise | 150 Degrees Celsius |
| Mounting Type | Floor |
| Primary Voltage | 480Δ |
| Product Category | Dry Type Distribution Transformer |
| Secondary Voltage | 480Y/277 V |
| Taps % Steps | 2.5% |
| UL Insulation Class | 220°C |
| UPC | 047503093061 |
| Winding Material | AL |
| kVA | 45 |

Dimensions

| | |
|--------|----------|
| Height | 25.5 in |
| Length | 19.37 in |
| Weight | 400 lb |
| Width | 24.39 in |

Electrical Ratings

| | |
|------------------|--------|
| Efficiency | 98.40% |
| Frequency Rating | 60 Hz |
| Primary Voltage | 480D V |

Certifications and Compliance

| | |
|--------------|--------------|
| CSA Standard | C22.2 No. 47 |
|--------------|--------------|

| | |
|---------------------------|--|
| Dept of Energy Regulation | Meets or exceed U.S. DOE 10 CFR Part 431 |
| Nema Rating | NEMA 3R |
| UL Standard | UL 1561 |