



\* Representative image

## T3075K0013BSB

by Acme Electric  
Catalog ID: T3075K0013BSB

Prop65\_Cancer

Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V,  
75kVA, 80°C, Shielded

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

### Product Details

#### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	80 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503093146
Winding Material	AL
kVA	75

#### Dimensions

Height	35.47 in
Length	26.88 in
Weight	698 lb
Width	31.9 in

#### Electrical Ratings

Efficiency	98.60%
Frequency Rating	60 Hz
Primary Voltage	480D V

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561