



## T3075K0034B

by Acme Electric  
Catalog ID: T3075K0034B

Low Voltage Distribution Transformer - Three Phase, 208Δ - 480Y/277V  
75kVA

- Quiet operation with sound levels below NEMA standards

### Product Details

#### General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	2.5%
UL Insulation Class	220°C
Winding Material	AL
kVA	75

#### Dimensions

Height	29.41 in
Length	22.37 in
Weight	530 lb
Width	28.15 in

#### Electrical Ratings

Efficiency	98.60%
Frequency Rating	60 Hz
Primary Voltage	208D V

#### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R

UL Standard	UL 1561
-------------	---------