



\* Representative image

## T3075K0083BS

by Acme Electric  
Catalog ID: T3075K0083BS

Prop65\_Cancer

Low Voltage Distribution Transformer - Three Phase, 600Δ - 208Y/120V, 75kVA, Shielded

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503093221
Winding Material	AL
kVA	75

### Dimensions

Height	29.41 in
Length	22.37 in
Weight	600 lb
Width	28.15 in

### Electrical Ratings

Efficiency	98.60%
Frequency Rating	60 Hz
Primary Voltage	600D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561