



* Representative image

T3112K0023B

by Acme Electric
Catalog ID: T3112K0023B

Prop65_Cancer

Low Voltage Distribution Transformer - Three Phase, 480Δ - 240Δ/120V, 112.5kVA

- Quiet operation with sound levels below NEMA standards

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	240D 120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503093337
Winding Material	AL
kVA	112.5

Dimensions

Height	35.47 in
Length	26.88 in
Weight	750 lb
Width	31.9 in

Electrical Ratings

Efficiency	98.74%
Frequency Rating	60 Hz
Primary Voltage	480D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561