



* Representative image

T3150K0044B

by Acme Electric

Catalog ID: T3150K0044B

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 240Δ - 208Y/120V, 150kVA

- Quiet operation with sound levels below NEMA standards

Product Details

General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503093412
Winding Material	AL
kVA	150

Dimensions

Height	41.52 in
Length	29.87 in
Weight	978 lb
Width	32.9 in

Electrical Ratings

Efficiency	98.83%
Frequency Rating	60 Hz
Primary Voltage	240D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561