



T3150K0074B

by Acme Electric
Catalog ID: T3150K0074B

240Δ Primary Volts - 480Y/277 Secondary Volts - 3Ø.

- Quiet operation with sound levels below NEMA standards

Product Details

General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	2.5%
UL Insulation Class	220°C
Winding Material	AL
kVA	150

Dimensions

Height	41.52 in
Length	29.87 in
Weight	973 lb
Width	32.9 in

Electrical Ratings

Efficiency	98.83%
Frequency Rating	60 Hz
Primary Voltage	240D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R

UL Standard	UL 1561
-------------	---------