



T3225K0083BS

by Acme Electric
Catalog ID: T3225K0083BS

600Δ Primary Volts - 208Y/120 Secondary Volts - 3Ø.

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Electrostatic Shield	Shielded
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	600Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	220°C
Winding Material	AL
kVA	225

Dimensions

Height	41.52 in
Length	29.87 in
Weight	1200 lb
Width	32.9 in

Electrical Ratings

Efficiency	98.94%
Frequency Rating	60 Hz
Primary Voltage	600D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431

Nema Rating	NEMA 3R
UL Standard	UL 1561