



* Representative image

T3300K0034B

by Acme Electric

Catalog ID: T3300K0034B

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 208Δ - 480Y/277V
300kVA

- Quiet operation with sound levels below NEMA standards

Product Details

General

ANFC Taps	2
BNFC Taps	2
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	208Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503094693
Winding Material	AL
kVA	300

Dimensions

Height	45.6 in
Length	35.5 in
Weight	1550 lb
Width	39.5 in

Electrical Ratings

Efficiency	99.02%
Frequency Rating	60 Hz
Primary Voltage	208D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561