



\* Representative image

## T3300K0053B

by Acme Electric

Catalog ID: T3300K0053B

Prop65\_Cancer&amp;Reproductive

Low Voltage Distribution Transformer - Three Phase, 480Δ - 480Y/277V, 300kVA

- Quiet operation with sound levels below NEMA standards

## Product Details

### General

ANFC Taps	2
BNFC Taps	4
Construction	Ventilated
Max Temperature Rise	150 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	2.5%
UL Insulation Class	220°C
UPC	047503093573
Winding Material	AL
kVA	300

### Dimensions

Height	45.6 in
Length	35.5 in
Weight	1600 lb
Width	39.5 in

### Electrical Ratings

Efficiency	99.02%
Frequency Rating	60 Hz
Primary Voltage	480D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Dept of Energy Regulation	Meets or exceed U.S. DOE 10 CFR Part 431
Nema Rating	NEMA 3R
UL Standard	UL 1561