



\* Representative image

## T335000153S

by Acme Electric  
Catalog ID: T335000153S

Prop65\_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 480Δ - 480Y/277V, 15kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

## Product Details

### General

ANFC Taps	2
BNFC Taps	4
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	480Y/277 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503731680
Winding Material	AL
kVA	15

### Dimensions

Height	18.86 in
Length	9.03 in
Weight	250 lb
Width	20.3 in

### Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

### Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 3R
UL Standard	UL 506