



* Representative image

T3533611S

by Acme Electric
Catalog ID: T3533611S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 240Δ - 208Y/120V, 15kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	240Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	5.0%
UL Insulation Class	180°C
UPC	047503733950
Winding Material	AL
kVA	15

Dimensions

Height	18.86 in
Length	9.03 in
Weight	250 lb
Width	20.3 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	240D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R

UL Standard	UL 506
-------------	--------