



* Representative image

T379083S

by Acme Electric
Catalog ID: T379083S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase,
190/200/208/220/240Δ - 400Y/231V, 15kVA

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	190 / 200 / 208 / 220 / 240Δ V
Product Category	Dry Type Distribution Transformer
Secondary Voltage	400Y/231 V
UL Insulation Class	180°C
UPC	047503166000
Winding Material	CU
kVA	15

Dimensions

Height	18.86 in
Length	9.03 in
Weight	300 lb
Width	20.3 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	190/200/208/220/240D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
Nema Rating	NEMA 3R
UL Standard	UL 506