



* Representative image

T3793123S

by Acme Electric
Catalog ID: T3793123S

Prop65_Cancer&Reproductive

Low Voltage Distribution Transformer - Three Phase, 480Δ - 208Y/120V, 30kVA, Encapsulated

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

Product Details

General

ANFC Taps	2
BNFC Taps	4
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Floor
Primary Voltage	480Δ
Product Category	Dry Type Distribution Transformer
Secondary Voltage	208Y/120 V
Taps % Steps	2.5%
UL Insulation Class	180°C
UPC	047503183007
Winding Material	CU
kVA	30

Dimensions

Height	24.81 in
Length	11.14 in
Weight	613 lb
Width	27.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

Certifications and Compliance

CSA Standard	C22.2 No. 47
--------------	--------------

Nema Rating	NEMA 3R
UL Standard	UL 506